





ALD Vacuum Technologies

High Tech is our Business

METAL ADDITIVE MANUFACTURING



EIGA and VIGA: Metal Powder Inert Gas Atomization Equipment



VIGA

Vacuum Induction-melting Inert Gas Atomization


- **Leading process** for production of powder feedstock for Metal Additive Manufacturing of superalloys and dental alloys such as **In738, In718, In625, CoCr**
- **Superclean powder** due to melting under vacuum/inert conditions
- **Spherical powder morphology** with high tap density due to inert gas atomization
- **Plant sizes from 20 t up to 2000 t p.a.**
- **Repeatable product quality and particle size distribution**



Dental part CoCr alloy*



Turbine blade Inconel 718*




Particle Size Distribution

* Courtesy of SLM Solutions

EIGA

Electrode Induction-melting Inert Gas Atomization

- **Leading process** for production of powder feedstock for Metal Additive Manufacturing of refractory and reactive alloys such as **CP-Ti, TiAl6V4, TiAl, Zr702** and precious metals
- **Superclean powder** due to induction ceramic-free melting
- **Spherical powder morphology** with high tap density due to inert gas atomization
- Melting and atomization without refractory consumable crucible
- **Robust, repeatable process**



Medical implant
TiAl6V4 alloy *

EIGA

High Quality Titanium Powder for Metal Additive Manufacturing

- An alloy barstick is fed at constant speed vertically from the top into a conical induction coil.
- A high-frequency electromagnetic field induces Eddy-currents in the barstick which starts to form a melt film at the conical surface.

- The melt film flows to the cone tip and melt drops separate. A constant melt flow evolves after start-up and flows vertically into the inert gas nozzle.
- The process enables melting and inert gas atomizing of refractory and/or reactive alloys without a ceramic liner or cold wall.

■	VIGA Powder for Metal Additive Manufacturing In625, 718, 738 CoCrMo(W)
■	EIGA Powder for Metal Additive Manufacturing CP-Ti Zr702 TiAl6V4 Precious TiAl Metals

250 μm



ALD

High value and high standards

- Many years of experience in design and manufacturing of vacuum inert gas atomizers in the superalloys, thermal spray, titanium, precious metals and electronics industries
- Worldwide sales and service network
- Testing facilities for powder production available in Germany



Technical Data **ATOMIZER EQUIPMENT**

	VIGA	EIGA
Equipment Overall Height	9 - 16 m	7 - 10 m
Equipment Footprint	8 x 8 m	5 x 5 m
Connected Power	80 - 1500 kVA	80 - 300 kVA
Ultimate Vacuum	5 Pa	5 Pa
Leak Rate	5 Pa l/s	5 Pa l/s

Technical Data **ATOMIZATION PROCESS**

	VIGA	EIGA
Annual Powder Production Capacity	50 - 2000 MT	50 - 250 MT
Atomization Gas	N ₂ or Ar	Ar or N ₂
Atomization Gas Pressure	20 - 60 bar	15 - 35 bar
Atomization Gas Flowrate	15 - 40 m ³ /min (STP)	8 - 18 m ³ /min (STP)
Min. Batch Size	5 - 2000 kg	5 - 100 kg

Technical Data **METAL POWDER**

	VIGA	EIGA
Typical Powder Alloys for Metal AM	CoCrMo(W), In625, In718, In738	CP-Ti, TiAl6V4, TiAl, Zr702, precious metals
Powder Morphology	spherical	spherical
d ₅₀ (PSD Mass Median)	35 - 70 µm	60 - 100 µm
Typical/ Available Size Classes for Metal AM	- 45 µm +10 - 45 µm +25 - 45 µm +45 - 63 µm +45 - 105 µm	- 45 µm +10 - 45 µm +25 - 45 µm +45 - 63 µm +45 - 105 µm

ALD Vacuum Technologies GmbH

Otto-von-Guericke Platz 1
63457 Hanau, Germany
Phone +49 (0) 6181 307-0
Fax +49 (0) 6181 307-3290
E-Mail info@ald-vt.de
Internet www.ald-vt.com

USA/Canada

ALD Vacuum Technologies Inc.
18 Thomson Road
East Windsor, CT 06088, USA
Phone +1 (860) 386 7227
E-Mail info@ald-usa.com

Far East (Japan/Korea/Taiwan)

**ALD Thermo Technologies
Far East Co., Ltd.**
Shinjuku Nomura Bldg. 6F
1-26-2 Nishi Shinjuku
Shinjuku-ku
Tokyo 163-0558, Japan
Phone +81 (3) 3340 3726
E-Mail peter.lang@ald-vt.de

China

**ALD-C&K Vacuum Technologies
(Suzhou) Co. Ltd.**
333 Yegang Road
Wujiang Economic and
Technological Development Zone
Suzhou, 215200, P. R. China
Phone +86 512 6385 8833
E-Mail info@ald-cn.com

Russia

ALD Vacuum Technologies GmbH
Daev per., 20
Moskau, Russia
Phone +7 (495) 787 6733
E-Mail ald@metallurg.com.ru